





PCB LAYOUT(Tolerance:±0.05)

REV	DESCRIPTION	DESIGN	DATE
A0	NEW RELEASE		2025/07/08

SCALE:1/2



Specifications:

Contact resistance:≤10mΩ
Insulation resistance:≥1000MΩ
Rated voltage:250V AC DC
Rated current:5.0A AC DC
Withstand Voltage: 1000V AC/minute
Temperature Range:−40℃~+125℃
Housing:LCP UL94V-0,BLACK
Contacts:Brass/MATTE Sn-plated
Solder Tabs:Brass/MATTE Sn-plated

ORDER INFORMATION:

A3006R-XP-F9KB3-R

PART No. _____
No.OF CIRCUITS: _____
PLASTIC MATERIAL: _____
F9K=LCP

PACKAGING: _____
R=REEL

Metal code: _____
3=Brass
PLATING: _____
B=MATTE Sn

PIN	DIM A	DIM B
2	3.00	9.65
3	6.00	12.65
4	9.00	15.65
5	12.00	18.65
6	15.00	21.65
7	18.00	24.65
8	21.00	27.65
*9	24.00	30.65
*10	27.00	33.65
*11	30.00	36.65
*12	33.00	39.65

浙江创都电子科技有限公司

TITLE: MX3.0单排卧贴

GENERAL TOLERANCE		USE:		PART NO.:	
X.	±0.50	X.	±5°	CAX-MX3.0-D0**WB-XT	
X.X	±0.30	X.X	±2°	DWG NO.:	
X.XX	±0.20	X.XX	±1°	SCALE	
UNITS: mm		DR:		1 : 1	SHEET 1 / 1