






RECOMMENDED P.C.B. LAYOUT
UNSPECIFIED TOLERANCE: ± 0.05
(TOP VIEW)

SPECIFICATION

1. Rating : DC 20V 10.0A(PIN $\varnothing 3.0$);
2. Contact resistance: $\leq 30\text{m}\Omega$;
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC500V);
4. Withstand voltage: 500VAC ;
5. Insertion and extraction force: 3-30N;
6. life test: 5,000 cycles;
7. Operation temperature range: $-20^{\circ}\text{C} \sim 70^{\circ}\text{C}$;
8. Preservative temperature range: $-25^{\circ}\text{C} \sim 75^{\circ}\text{C}$;



6	基座	1	PBT	黑色
5	后盖	1	PBT	黑色
4	平片	1	H62(Y)T: 0.50mm	Plated Ag
3	簧片	1	QSn6.5-0.1Y T: 0.25mm	Plated Ag
2	弯片	1	H62(Y)T: 0.5mm	Plated Ag
1	插针	1	H62 $\square$ D:0.30mm	Plated Sn

MODEL NO. DC JACK

Schematic

CIRCUIT DIAGRAW

序号	名称	数量	材料	备注
----	----	----	----	----

ECN NO	REV	DATE	DESCRIPTION	CHANGE	CHECK	APPRO	UNSPECIFIED TOLERANCE
—	A/0	NEW					
1	2	3	4	5	6	7	8

Designed:

Checked:

Approved:

Date:

2016/1/15

MODEL TYPE:

DC JACK

浙江创都电子科技有限公司

PART NO.
CAX-DC-062-10A-3.0-XL

UNIT:	SCALE:	VIEW:	Edition:
mm	1:1		A/0