

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40℃ to +105℃



Contact Material:Brass

Contact Plating:Au or Sn Over Ni



Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30-60 seconds
(260℃ for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

F 2 D 2 13 3 5 01 1 1280
产品类型 间距 塑胶高度 排数 单排PIN数 产品形态 塑胶材料 电镀厚度 包装方式 序列号
F=排母 2=2.0 D=4.3 2=双排 1=40P 3=SMT 5=PA6T 00=常规 01=1u" 02=2u" 03=3u" 1=管装 2=卷装 3=盒装 4=袋装 5=盒装

Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001	4.6		6.2	4.3	4.5
002					

				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30					UNIT		
				X.XX	±0.20	CHECK			SIZE	A4	PART NO.	1020200405
A0	2012.07.23	NEW DRAWING		X.XXX	±0.10				SHEET	1/1		
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle	±3°	APPROVE			PROJ.		TITLE:	2.0FH H=4.3 W=4.5 2*13P SMT=6.2 总高 4.6 U型 AU1U 青铜 PA6T
				DIM	TOL							