






REV.	ECN NO.	MODIFIED MARK	APPROVED
B		FIRST RELEASE	




COLOR TABLE

CODE	A	B
COLOR	WHITE	RED



PCB LAYOUT
TOP VIEW



SCHEMATIC

NOTES:
ELECTRICAL:
1:RATED CURRENT: 1A Max.
2:RATED VOLTAGE: 12V DC.
3:CONTACT RESISTANCE: 30 MILLIOHMS Max.
AFTER TESTING:100 MILLIOHMS Max.
4:INSULATION RESISTANCE: 100 MEGAOHMS Min.
5:DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC Min.
MECHANICAL:
1:INSERTION FORCE: 3N-30N.
2:WITHDRAWAL FORCE: 3N-30N.
3:DURRABILITY: 500 CYCLES.
ENVIRONMENTAL:
TEMPERATURE RANGE: -20°C TO 60°C.
MARK “▼” AS THE KEY CONTROL SIZE.
PIN PIN POSITION SIZE IS SUBJECT TO PCB BOARD.

⑤	COVER	1	ABS	BLACK	RoHS2.0
④	TERMINAL-A	2	BRASS t=0.5	CuSn PLATED	
③	SOCKET	1	BRASS t=0.36	CuSn PLATED	
②	WASHER	2	PBT	SEE COLOR TABLE	
①	HOUSE	1	ABS	WHITE	
NO.	PART NAME	Q'TY	MATERIAL	FINISH/COLOR	REMARK
ANGLE		±5°	MODEL NAME: (PART NO.) 浙江创都电子科技有限公司		
63 < L		±0.5			
16 < L ≤ 63		±0.4			
4 < L ≤ 16		±0.3			
L ≤ 4		±0.2			
TOL TABLE:					
		MAT'L: See table	DESIGN 07/29'23 TITLE: RCA PIN JACK		
		FINISH: See table	CHECKED 07/29'23 DWG NO.: CAX-AV-206B-WR-HP REV.: B		
		Q'TY:/	APPROVED: 07/29'23 UNIT: VIEW: SCALE: SHEET: SIZE: mm 5:1 1/1 A3		