










SECTION A-A




RECOMMENDED PCB LAYOUT
TOP VIEW TOLERANCE:±0.05



MATING PLUG
DP550250-0188-60000H

SPECIFICATION:

1. RATING: DC 20V 20A
2. CONTACT RESISTANCE:
30mΩ MAX.(INITIAL)
50mΩ MAX.(FINAL)
3. INSULATION RESISTANCE: 100 MΩ MIN.
4. WITHSTAND VOLTAGE: 500 VAC
5. INSERTION FORCE: 3N~30N
6. EXTRACTION FORCE: 3N~30N
7. DURABILITY: 5,000 CYCLES



E	CAP	PA 10T	BLACK	
D	GROUND	SUS 304		1
C	SHELL	C5210	Ni 40u"MIN.	1
B	CENTER PIN	H59	GOLD FLASH/Ni 40u" MIN.	1
A	HOUSING	PA 10T	BLACK	1
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

UNLESS OTHERWISE
SPECIFIED TOLERANCES

浙江创都电子科技有限公司				PART NAME: Φ5.5 立式(H=13.0) DC POWER JACK	
DESIGN:				PART NO. CAX-DC-1392-200H-2.5-AUXL L	
CHECK:				SHEET: 1/1 REV.: A1	
APPROVED				DRAWING NO	
DECIMALS:		ANGLES:		UNIT: mm	
DIM	TOL	DIM	TOL	3RD ANGLE PROJECTION	
X.	±0.50	X.	±2°		
X.X	±0.30	X.X	±1°		
X.XX	±0.20	X.XX			
X.XXX	±0.10	X.XXX			

REV.	ECN NO.	DESCRIPTION	DESIGN	DATE
------	---------	-------------	--------	------