


REV	DESCRIPTION	DESIGN	DATE
A0	NEW RELEASE		2025/07/08



PIN	DIM	ADIM	B
2x2	3.00	9.65	
2x3	6.00	12.65	
2x4	9.00	15.65	
2x5	12.00	18.65	
2x6	15.00	21.65	
2x7	18.00	24.65	
2x8	21.00	27.65	
2x9	24.00	30.65	
2x10	27.00	33.65	
2x11	30.00	36.65	
2x12	33.00	39.65	





Specifications:
Contact resistance:≤10mΩ
Insulation resistance:≥1000MΩ
Rated voltage:250V AC DC
Rated current:5.0A AC DC
Withstand Voltage: 1000V AC/minute
Temperature Range:-25℃~+85℃
Housing:LCP UL94V-0,BLACK
Contacts:Brass/MATTE Sn-plated
Solder Tabs:Brass/MATTE Sn-plated

ORDER INFORMATION:

A3006R-2XXP-F9KB3-R		PACKAGING: R=REEL
PART No.		
No.OF CIRCUITS:		Metal code: 3=Brass
04-24		PLATING: B=MATTE Sn
PLASTIC MATERIAL:		
F9K=LCP		



PCB LAYOUT(Tolerance:±0.05)



浙江创都电子科技有限公司				TITLE:MX3.0双排卧贴	
GENERAL		TOLERANCE		USE: CUSTOMER	
X.	±0.50	X.	±5°	APPD:	
X.X	±0.30	X.X	±2°	CHKD:	
X.XX	±0.20	X.XX	±1°	DR:	
UNITS: mm		DR:		SCALE 1 : 1	
PART NO.:		CAX-MX3.0-S0*WB-XT		SHEET 1 / 1	