





PCB LAYOUT(Tolerance:±0.05)

REV	DESCRIPTION	DESIGN	DATE
A0	NEW RELEASE		2025/07/08

SCALE:1/2




Specifications:

Contact resistance:≤10mΩ
Insulation resistance:≥1000MΩ
Rated voltage:250V AC DC
Rated current:5.0A AC DC
Withstand Voltage: 1000V AC/minute
Temperature Range:−40℃~+125℃
Housing:LCP UL94V−0,BLACK
Contacts:Brass/MATTE Sn−plated
Solder Tabs:Brass/MATTE Sn−plated

ORDER INFORMATION:

PART No.		A3006R-XP-F9KB3-R		PACKAGING: R=REEL	
No.OF CIRCUITS:		02-12		Metal code: 3=Brass	
PLASTIC MATERIAL:		F9K=LCP		PLATING: B=MATTE Sn	

PIN	DIM A	DIM B
2	3.00	9.65
3	6.00	12.65
4	9.00	15.65
5	12.00	18.65
6	15.00	21.65
7	18.00	24.65
8	21.00	27.65
*9	24.00	30.65
*10	27.00	33.65
*11	30.00	36.65
*12	33.00	39.65

浙江创都电子科技有限公司				TITLE: MX3.0单排卧贴	
GENERAL TOLERANCE		USE: CUSTOMER		PART NO.: CAX-MX3.0-D0**WB-XT	
X. ±0.50	X. ±5°	APPD:			
X.X ±0.30	X.X ±2°	CHKD:		DWG NO.:	
X.XX ±0.20	X.XX ±1°				
		DR:		SCALE 1 : 1	
UNITS: mm				SHEET 1 / 1	