











PCB MOUNTING HOLES

BOTTOM VIEW
(TOLERANCE: ±0.05)



SCHEMATIC

ELECTRICAL
VOLTAGE RATING: 20V DC (R.M.S)
CURRENT RATING: 10A
CONTACT RESISTANCE: 30mΩ MAX.
INSULATION RESISTANCE: 100 MΩ MIN.
DIELECTRIC WITHSTAND VOLTAGE: 500V AC (R.A.M)
TEMPERATURE RANGE: -25°C TO +85°C
MATERIALS & PLATING: SEE THE TABLE BELOW.

ANGULAR	±5°
16 < L ≤ 63	±0.4
4 < L ≤ 16	±0.3
L ≤ 4	±0.2
UNSPECIFIED TOLERANCE	

LTR	PART NAME	QTY	MATERIAL (THICK, COLOR)	REMARK
6	GROUND	1	SUS 304 0.15t	
5	SHELL	1	SPCC-SD 0.4t	CuSn-PLATING
4	TERMINAL	1	SUS 301 0.3t	
3	PIN	1	BRASS BAR	AU-PLATING
2	SPRING	1	COPPER ALLOY 0.3t	CuSn-PLATING
1	HOUSING	1	HIGH TEMP.THERMOPLASTIC PA9T	UL 94V-0

DSND	DATE	SCALE: 1:1	NAME DC 电源插座	
CHKD	DATE	VIEW:	CAT.NO.	
APVD	DATE	UNIT: mm	CAX-DC-0050-2.5-AU-10A-XL	
浙江创都电子科技有限公司			DWN.NO.	REVISION