




REV.	ECN. NO.	APPD.	DATE
A	C09089	JOYE	2009.6.17

ELECTRICAL
VOLTAGE RATING:20V DC (R.M.S)
CURRENT RATING:10 A
CONTACT RESISTANCE:30mΩ MAX.
INSULATION RESISTANCE:100 MΩ MIN.
DIELECTRIC WITHSTAND VOLTAGE:500V AC (R.A.M)
TEMPERATRUE RANGE:-25°C TO +85°C
MATERIALS & PLATING: SEE THE TABLE BELOW.



ORDERING INFORMATION:




PULG



SCHEMATIC



PCB LAYOUT
(TOLERANCE: ±0.05)



5	SHEEL	1	H65 0.3t	NI-PLATING
4	TERMINAL	1	H65 0.25t	CuSn-PLATING
3	PIN	1	H59	Ag-PLATING
2	SPRING	1	C5191 0.25t	CuSn-PLATING
1	HOUSING	1	PA9T UL 94V-0	BLACK
LTR	PART NAME	QTY	MATERIAL(THICK,COLOR)	REMARK

TITLE: DC POWER JACK 6PIN				浙江创都电子科技有限公司			
TOLERANCE		APP.		UNITS ☑ mm □ inch	PART NO. CAX-DC-0052-2.5-10A-XL		
LINEAR	ANGLE				SIZE A4		
16~63 ±0.4	x' ±5'	CHK.			DWG. NO.		
4~16 ±0.3	.x' ±2'						
≤ 4 ±0.2	.xx' ±1'	DRW.			SCALE FIT		
PRJ.	REV. A				SHEET 1 OF 1		

CUSTOMER DRAWING

