









2-1. INSERTION FORCE : 0.3~3.0 KGF
2-2. WITHDRAWAL FORCE : 0.3~3.0 KGF
3. LIFE TEST: 5,000 CYCLES MIN.



MATING PLUG $\varnothing 5.50$



RECOMMEND P.C.B LAYOUT
TOP VIEW (TOLERANCES:0.05)




 #1 CENTER PIN(+)
 #3 SHUNT TERMINAL
 #2 TIP SPRING(-)

ALL SELL	DIM "A"	DIM "B"
DC-208-3	0.90	1.7
DC-208-4	1.40	1.7
DC-208-5	2.25	1.3

G	GROUNDING	1	SUS301 0.1T	N/A
F	SHIELDING	1	C2680 0.35T	Ni 50u"
E	PIN	1	H59	Ni 50u"
D	STOPPER	1	SUS301 0.30T	cleaning
C	SHUNT TERMINAL	1	C2680 0.3T	Aq 5U" Ni50u" Plating
B	TIP SPRING	1	C5191 0.30T	Aq 5U" Ni50u" Plating
A	BODY	1	LCP	BLACK
NO.	DESCRIPTION	QTY	MATERIAL	PLATING & COLOR

							ANGLE	±5°	Designed:	Checked:	Approved:	Date: 2021/12/29	MODEL TYPE: DC JACK									
							30 ~	±0.30					浙江创都电子科技有限公司				PART NO. CAX-DC-208-3-2.5-XL					
							10 ~ 30	±0.20	UNIT:								SCALE:		VIEW:		Edition:	
—	A/O		NEW	—	—	—	~ 10	±0.10	mm								1:1				A/O	
ECN NO	REV	DATE	DESCRIPTION	CHANGE.	CHECK.	APPRO.	UNSPECIFIED TOLERANCE															