









PCB LAYOUT
TOP VIEW



SCHEMATIC

NOTES:
ELECTRICAL:
1:RATED CURRENT: 1A Max.
2:RATED VOLTAGE: 12V DC.
3:CONTACT RESISTANCE: 30 MILLIOHMS Max.
AFTER TESTING:100 MILLIOHMS Max.
4:INSULATION RESISTANCE: 100 MEGAOHMS Min.
5:DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC Min.
MECHANICAL:
1:INSERTION FORCE: 3N-30N.
2:WITHDRAWAL FORCE: 3N-30N.
3:DURRABILITY: 500 CYCLES.
ENVIRONMENTAL:
TEMPERATURE RANGE: -20°C TO 60°C.
MARK"▼"AS THE KEY CONTROL SIZE.
PIN POSITION AND SIZE OK IF FIT PCB BOARD

COLOR TABLE

CODE	A	B
COLOR	WHITE	WHITE
CODE	C	D
COLOR	RED	RED

⑤	COVER	2	ABS	BLACK	RoHS 2.0	
④	TERMINAL-A	4	BRASS t=0.5	CuSn PLATED		
③	WASHER	4	ABS	SEE COLOR TABLE		
②	SOCKET	2	BRASS t=0.36	CuSn PLATED		
①	HOUSE	1	ABS	WHITE		
NO.	PART NAME	Q'TY	MATERIAL	FINISH/COLOR	REMARK	
ANGLE		±5°	MODEL NAME: (PART NO.)		浙江创都电子科技有限公司	
63 < L		±0.5				
16 < L ≤ 63		±0.4				
4 < L ≤ 16		±0.3				
L ≤ 4		±0.2	MAT'L: DESIGN: 07/25'23 TITLE: RCA PIN JACK			
TOL TABLE:		See table	See table			
		FINISH: See table	CHECKED: 07/25'23			DWG NO: CAX-AV-410B-WR-HP
		Q'TY:/	APPROVED: 07/25'23	UNIT: mm		VIEW: 
				SCALE: 5:1		SHEET: 1/1
						SIZE: A3