










A-A



SCHEMATIC



PCB HOLES (THE PATTERN SIDE)

SPECIFICATION

1. Rating : DC 20V 4A;
2. Contact resistance: $\leq 30m\Omega$;
3. Insulation resistance: $\geq 100M\Omega$ (DC250V);
4. Withstand voltage: 500VAC ;
5. Insertion and extraction force: 3-30N;
6. life test: 5,000 cycles.

△ X	EXCHANGE DESCRIPTION	DATE	REVISED	APVD	Angle	±5°
△ X					63 < L	±0.5
△ X					16 < L ≤ 63	±0.4
△ X					4 < L ≤ 16	±0.35
REMARK					L ≤ 4	±0.25
REVISIONS					UNLESS TOLERANCE	

5	CENTER PIN		1	BRASS	Ni
4	PIN TERMINAL	3	1	BRASS t=0.4	Sn
3	BREAK TERMINAL	2	1	BRASS t=0.5	Sn
2	TIP SPRING	1	1	C5191 t=0.25	Sn
1	HOUSING		1	PBT UL94 V=0	Black
NO.	PART NAME	TER.NO.	QT'Y	MATERIAL	REMARK
DSND		DATE		SCAL: 1:1	NAME: DC JACK
CHKD		DATE		VIEW:	CAT.NO:
APVD		DATE		UNIT:	CAX-DC-091-4A-2.0-XL
浙江创都电子科技有限公司				DWG.NO.	REVISED
					A/0