







P. C. B Layout
(Copper-sided view)



Model NO.	DC-044AL
Schematic	

SPECIFICATION

- Rating : DC 25V 3.0A;
- Contact resistance: $\leq 50\text{m}\Omega$;
- Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V);
- Withstand voltage: 500VAC ;
- Insertion and extraction force: 3-30N;
- life test: 5,000 cycles.

6	SHEEL	1	C2680	Ni-PLATED
5	TERMINAL	1	C2680	Ag-PLATED
4	SHRAPNEL	1	C5191	Ag-PLATED
3	TERMINAL	2	C2680	Ag-PLATED
2	PIN	1	BRASS	CuSn-PLATED
1	HOUSING	1	PA9T	BLACK
No.	NAME	QTY.	MATERIAL	FINISH/COLOR

Designed:	Checked:	Approved:	Date: 2018/06/28	MODEL TYPE: DC JACK
-----------	----------	-----------	---------------------	------------------------

浙江创都电子科技有限公司

PART NO. CAX-DC-044AL-3A-2.5-XL			
UNIT:	SCALE:	VIEW:	Edition:
mm	1:1		A/0

						ANGLE	±5°
						30 ~	±0.30
						10 ~ 30	±0.20
						~ 10	±0.10
ECN NO	REV	DATE	DESCRIPTION	CHANGE	CHECK	APPRO.	UNSPECIFIED TOLERANCE
1							