





REV	DESCRIPTION	DESIGN	DATE
A0	NEW RELEASE		2025/07/08






Specifications:
Contact resistance:≤10mΩ
Insulation resistance:≥1000MΩ
Rated voltage:250V AC DC
Rated current:5.0A AC DC
Withstand Voltage: 1000V AC/minute
Temperature Range:-40℃~+125℃
Housing:LCP UL94V-0,BLACK
Contacts:Brass/MATTE Sn-plated
Solder Tabs:Brass/MATTE Sn-plated
CAP:Stainless steel

ORDER INFORMATION:

A3005V-XP-F9KB3-R-X

PART No. _____
No.OF CIRCUITS: _____
Q2P=12P
PLASTIC MATERIAL: _____
F9K=LCP

X:CAP
PACKAGING:
R=REEL
Metal code:
J=Brass
PLATING:
B=MATTE Sn



PIN	DIM	ADIM	B
2	3.00	9.65	
3	6.00	12.65	
4	9.00	15.65	
5	12.00	18.65	
6	15.00	21.65	
7	18.00	24.65	
8	21.00	27.65	
*9	24.00	30.65	
*10	27.00	33.65	
*11	30.00	36.65	
*12	33.00	39.65	

浙江创都电子科技有限公司			TITLE: MX3.0单排立贴	
GENERAL TOLERANCE		USE: CUSTOMER	PART NO.:	
X. ±0.50	X. ±5°		CAX-MX3.0-DO**LA-XT	
X.X ±0.30	X.X ±2°	APPD:	DWG NO.:	
X.XX ±0.20	X.XX ±1°	CHKD:		
UNITS: mm		DR:	SCALE 1 : 1	SHEET 1 / 1