







Electrical

Current rating: 1.5 AMPS

Voltage rating: 125V AC

Insulation resistance: $\geq 500\text{m}\Omega$

Withstanding voltage: AC 1000V MS

50HZ 或 60Hz Min

Contact rating: $\leq 30\text{ m}\Omega$ Working temperature: $-40^{\circ}\text{C} \sim +70^{\circ}\text{C}$

机构特性:

1. 塑壳材质: PBT、PA46、PA66黑色
2. 圆针材质: 磷青铜, $\phi 0.46\text{mm}$
3. 圆针电镀: 镍底, 表面全部镀金
4. 外壳材质: 黄铜, 厚度0.2, 镀镍
5. 可靠性: 最少750次插拔
6. 插入力: 30N
7. 相对湿度: $< 80\%$



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X' $\pm 2^{\circ}$ X.X' $\pm 0.5^{\circ}$

UNIT: mm [inch]

SCALE: 1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

RJ45 90° DIP 1X2无灯带屏蔽

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW455-RJ45-210B

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2308101804

SHEET NO.

1 OF 1