










REV.	ECN. NO.	APPD.	DATE
A	C09089	JOYE	2009.6.17




SCHEMATIC



PCB LAYOUT
(TOLERANCE: ± 0.05)



PULG



5	SHEEL	1	H65 0.3t	NI-PLATING
4	TERMINAL	1	H65 0.25t	CuSn-PLATING
3	PIN	1	H59	Ag-PLATING
2	SPRING	1	C5191 0.25t	CuSn-PLATING
1	HOUSING	1	PA9T UL 94V-0	BLACK
LTR	PART NAME	QTY	MATERIAL(THICK,COLOR)	REMARK

TITLE:			DC POWER JACK 6PIN			浙江创都电子科技有限公司		
TOLERANCE		APP.		UNITS ☒ mm ☐ inch	PART NO.			
LINEAR	ANGLE				CAX-DC-0052C-3.0-10A-XL			
16~63 ±0.4	x.' ±5'	CHK.		SIZE A4	DWG. NO.			
4~16 ±0.3	.x' ±2'							
≤ 4 ±0.2	.xx' ±1'							
PRJ. 	REV. A	DRW.		SCALE FIT	SHEET 1 OF 1			