








REV.	ECN NO.	MODIFIED MARK	APPROVED
A	_____	FIRST RELEASE	



PCB LAYOUT
TOP VIEW



SCHEMATIC



GAUGE PLUG

COLOR TABLE

CODE	A	B
COLOR	WHITE	WHITE
CODE	C	D
COLOR	RED	RED

仅供参考

NOTES:

ELECTRICAL:

1:RATED CURRENT: 1A Max.

2:RATED VOLTAGE: 12V DC.

3:CONTACT RESISTANCE: 30 MILLIOHMS Max.

AFTER TESTING:100 MILLIOHMS Max.

4:INSULATION RESISTANCE: 100 MEGAOHMS Min.

5:DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC Min.

MECHANICAL:

1: INSERTION FORCE: 3N-30N.

2:WITHDRAWAL FORCE: 3N-30N.

3: DURABILITY: 500 CYCLES.

ENVIRONMENTAL :

TEMPERATURE RANGE: -20°C TO 60°C .

⑤	COVER	1	ABS	BLACK	RoHS2.0				
④	TERMINAL-A	4	BRASS t=0.5	CuSn PLATED					
③	SOCKET	2	BRASS t=0.4	CuSn PLATED					
②	WASHER	4	PBT	SEE COLOR TABLE					
①	HOUSE	2	ABS	WHITE					
NO.	PART NAME	Q'TY	MATERIAL	FINISH/COLOR	REMARK				
ANGLE		±5°	MODEL NAME: (PART NO.)		浙江创都电子科技有限公司				
63 < L		±0.5							
16 < L ≤ 63		±0.4							
4 < L ≤ 16		±0.3							
L ≤ 4		±0.2	MAT'L: See table	DESIGN:	TITLE: RCA PIN JACK				
TOL TABLE:			FINISH: See table	CHECKED:	DWG. NO.: CAX-AV-406B-WR-HP			REV.: A	
			Q'TY:/	APPROVED:	UNIT: mm	VIEW: 	SCALE: 5:1	SHEET: 1/1	SIZE: A3