






ROHS



NOTE:

- 1.MATING FORCE:3~30 N
- 2.UNMATING FORCE:3~30 N
- 3.CONTACT RESISTANCE: 30 MILL.OHM MAX
- 4.INSULATION RESISTANCE: 100 MEG.OHM MIN
- 5.DIELECTRIC WITHSTANDING VOLTAGE:500V/60S
- 6.DURABILITY: 5000 CYCLES
- 7.VOLTAGE/CURRENT RATING: DC 30V 1A
- 8.OPERATION TEMPERATURE: -40°C TO +80°C



PCB HOLES(TOP VIEW)
GENERAL TOLERANCE:±0.1mm

浙江创都电子科技有限公司

Unless Otherwise specified, Tolerance:		DESCRIBE: 电源插座 φ6.4/ 铜针 2.0mm LCP 黑色 贴片			
X	±0.50	SCALE:	1:1	Drawn	LQ 2021/08/12
X.x	±0.30	Unit:	mm	Check	SWG 2021/08/12
X.xx	±0.20	Size:	A4	Approve	XXF 2021/08/12
X.xxx	±0.10	CUSTOMER COPY			
ANGLES: ±3°					
		Part No:		Dwg No:	
		CAX-DC-067-2.0-XL		Sheet P1/1	
				Rev. A1	