









ELECTRICAL
VOLTAGE RATING:12V DC
CURRENT RATING:10A
CONTACT RESISTANCE:30mΩ MAX(INITIAL)
100mΩ MAX(FINAL)
INSULATION RESISTANCE: 100 MΩ MIN.
DIELECTRIC WITHSTAND VOLTAGE: 500V AC
DURABILITY TEST: 5,000 CYCLES.
TEMPERATURE RANGE: -25°C TO +75°C
MATERIALS & PLATING: SEE THE TABLE BELOW.
PACKAGING:PLASTIC BOX



PCB LAYOUT
TOP VIEW (Tolerance:±0.05)



8	SHELL	1	C5191 T=0.25mm	Ni Plated
7	6#-TERMINAL	3	SUS T=0.25mm	
6	5#-TERMINAL	1	C5191 t=0.2mm	GOLD FLASH ON CONTACT AREA 1u" ,ALL OVER 50u" NI.
5	4#-TERMINAL	1	C5191 t=0.25mm	
4	3#-TERMINAL	1	C5191 t=0.2mm	
3	2#-TERMINAL	1	C5191 t=0.2mm	
2	1#-TERMINAL	1	C5191 t=0.4mm	
1	HOUSING	1	PA9T UL94V-0	BLACK
NO.	PART NAME	QTY	MATERIAL	REMARK

环保
Green Product

ECN NO	REV	DATE	DESCRIPTION	CHANGE	CHECK	APPRO	UNSPECIFIED TOLERANCE
							ANGLE ±2°
							30 ~ ±0.30
	A/1		按实物更新pcb layout				10 ~ 30 ±0.20
	A/0		NEW				~ 10 ±0.15

Designed:	Checked:	Approved:	Date: 2016/12/13	MODEL TYPE: DC Jack			
浙江创都电子科技有限公司				PART NO. CAX-DC-105-5.95-10A-XL			
				UNIT:	SCALE:	VIEW:	Edition:
				mm	1:1		A/1