





ELECTRICAL
RATING:DC12V 1A:
CONTACT RESISTANCE:30mΩ MAX(INITIAL)
100mΩ MAX(FINAL)
INSULATION RESISTANCE: 100 MΩ MIN.
DIELECTRIC WITHSTAND VOLTAGE: 500V AC
DURABILITY TEST: 5,000 CYCLES.
TEMPERATURE RANGE: -25°C TO +75°C
MATERIALS & PLATING: SEE THE TABLE BELOW.
PACKAGING: TAPE&REEL



PCB LAYOUT
TOP VIEW (Tolerance:±0.05)

环保
Green Product

6	HOUSING	1	PA9T UL94V-0	BLACK
5	PIN	1	H59 φ1.3	Ni Plated
4	TERMINAL-4	1	BRASS T=0.25	Ag Plated
3	TERMINAL-3	1	BRASS T=0.25	
2	TERMINAL-2	1	C5191 t=0.3	
1	TERMINAL-1	1	BRASS T=0.25	
NO.	PART NAME	QTY	MATERIAL	REMARK

							ANGLE	±2°
							X.	±0.3
							.X	±0.25
	A/O		NEW				.XX	±0.15
ECN NO	REV	DATE	DESCRIPTION	CHANGE	CHECK	APPRO.	UNSPECIFIED TOLERANCE	

Designed: Checked: Approved: Date: 2018/08/11

浙江创都电子科技有限公司

MODEL TYPE: DC POWER JACK			
PART NO. CAX-DC-039A-1.3-XL			
UNIT:	SCALE:	VIEW:	Edition:
mm	1:1	⊙ ⊞	A/O