





REV.	ECN NO.	MODIFIED MARK	APPROVED
B			




PCB LAYOUT
TOP VIEW



SCHEMATIC

COLOR TABLE

CODE	A	B
COLOR	RED	WHITE



NOTES:
ELECTRICAL:
1:RATED CURRENT: 0.2A Max.
2:RATED VOLTAGE: 50V AC.
3:CONTACT RESISTANCE: 30 MILLIOHMS Max.
AFTER TESTING:100 MILLIOHMS Max.
4:INSULATION RESISTANCE: 100 MEGAOHMS Min.
5:DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC Min.
MECHANICAL:
1:INSERTION FORCE: 3N-30N.
2:WITHDRAWAL FORCE: 3N-30N.
3:DURRABILITY: 100 CYCLES.
ENVIRONMENTAL:
TEMPERATURE RANGE: -20°C TO 60°C.
MARK "▼" AS THE KEY CONTROL SIZE.
PIN PIN POSITION SIZE IS SUBJECT TO PCB BOARD.

⑦	COVER	1	ABS	BLACK	RoHS 2.0			
⑥	TERMINAL-C	1	SPCC t=0.5	CuSn PLATED				
⑤	TERMINAL-B	1	BRASS t=0.3	CuSn PLATED				
④	TERMINAL-A	1	BRASS t=0.3	CuSn PLATED				
③	WASHER	2	ABS	SEE COLOR TABLE				
②	SOCKET	2	BRASS t=0.36	CuSn PLATED				
①	HOUSE	1	ABS	BLACK				
NO.	PART NAME	Q'TY	MATERIAL	FINISH/COLOR	REMARK			
ANGLE		±5°		浙江创都电子科技有限公司				
63 < L		±0.5						
16 < L ≤ 63		±0.4						
4 < L ≤ 16		±0.3						
L ≤ 4		±0.2		TITLE: CAX-AV-207FB-RW-HP				
TOL TABLE:		MAT'L: See table	DESIGN:	DWG NO.:				
		FINISH: See table	CHECKED:	REV.: A				
		Q'TY:/	APPROVED:	UNIT: mm	VIEW: 	SCALE: 5:1	SHEET: 1/1	SIZE: A3