







PRODUCT NO: DS801FPR-0062

REV	DESCRIPTION	DWN	DATE	APPROVEN
A	FIRST ISSUE	W.cheng	2020/10/23	John kine
B	将原来16.00MM增长1.5MM	W.LI	2021/09/14	John kine



SPECIFICATIONS:

IMPEDANCE: 75 ohms
FREQUENCY RANGE: 0~4GHz
VSWR: 1.5MAX
WITHSTANDING VOLTAGE: 500V RMS@SEA LEVEL
INSULATION RESISTANCE: 5000 megohms min
TEMPERATURE RANGE: -55°C TO +155°C
RELATIVE TEMPERATURE: ≤ 95%(40°C±2°C)

PRODUCT NO	BODY SURFACE TREATMENT
DS801FPR-0062	NICKEL
DS801FPR-0062A	GOLD

1	BODY	BRASS		1	NOTE:	TOIERANCE	UNLESS OTHERWISE SPECIFIED TOLERANCES IN INCHES ARE 0.5-8MM±0.20MM 8-30MM±0.40MM 30-120MM±0.50MM		DOSIN INDUSTRIAL(HK)CO.,LTD 东莞市德索五金电子有限公司 Dongguan Dosin Hardware Electronics Co.,Ltd.	Web:http://www.dosinconn.com dosin2005@dosin-china.com E-mail: dosin2005@163.com Tel: (0086)769-81153906 Fax: (0086)769-81875836	
2	CONTACT PIN	BRASS	GOLD	1							
3	INSULATOR	TEFLON	WHITE	1							
4											
5					DRAWN	2021/09/14	VIEW		NAME:	BNC JACK CONNECTOR	
6											
7					CHECKED		UNIT	MM	SIZE B	PRODUCT NO: DS801FPR-0062	SIZE B
8											
9					APPROVALS		SCALE	1 : 1	DATE TIME 2021/09/14	CAD FILE D/companydrawings/BD	SHEET: 1 OF 1
10											
NO	COMPONENT NUMBER	MATERIAL	FINISH	QTY							
A		B	C	D	E		F		G		

DOSIN DOSIN INDUSTRIAL(HK)CO.,LTD
东莞市德索五金电子有限公司
Dongguan Dosin Hardware Electronics Co.,Ltd. Fax:(0086)769-81875836
Web: <http://www.dosinconn.com>
dosin2005@dosin-china.com
E-mail: dosin2005@163.com
Tel: (0086)769-81153906