






ELECTRICAL
RATING:DC 20V 10A:
CONTACT RESISTANCE:30mΩ MAX(INITIAL)
INSULATION RESISTANCE: 100 MΩ MIN.
DIELECTRIC WITHSTAND VOLTAGE: 500V AC
INSERTION FORCE:3-35N.
DURABILITY TEST: 5,000 CYCLES.
TEMPERATURE RANGE: -25°C TO +75°C
MATERIALS & PLATING: SEE THE TABLE BELOW.



(TOLERANCE ± 0.05)



环保
Green Product

7	SHELL	1	SPCC 0.4T	Ni 80u", Cu UNDERPLATED 80u"
6	SIGNAL	1	C5191 0.3T	GOLD FLASH ON CONTACT AREA 1u",
5	SPRING -	1	C5191 0.3T	MATT TIN 100u" ON SOLDER,
4	SPRING +	1	C5191 0.3T	Ni 40u" UNDERPLATED OVER ALL.
3	BACK PLATE	1	THERMOPLASTIC UL 94V-0 (HALOGEN FREE)	BLACK
2	COVER	1		
1	HOUSING	1		
NO.	PART NAME	QTY	MATERIAL	REMARK

							ANGLE $\pm 2^\circ$
							. = ± 0.30
							.X = ± 0.25
	A/0		NEW				.XX = ± 0.15
ECN NO	REV	DATE	DESCRIPTION	CHANGE	CHECK	APPRO.	UNSPECIFIED TOLERANCE

Designed:	Checked:	Approved:	Date: 2018/07/30	MODEL TYPE: DC POWER JACK
浙江创都电子科技有限公司				PART NO. CAX-DC-113-10A-7550-0.5XL
				UNIT: mm
				SCALE: 1:1
				VIEW:
				Edition: A/0