





SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60seconds
(260°C for 5seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
XY-PZ2.54VS-01-01P	1	0.00	2.54
XY-PZ2.54VS-01-02P	2	2.54	5.08
XY-PZ2.54VS-01-03P	3	5.08	7.62
XY-PZ2.54VS-01-04P	4	7.62	10.16
XY-PZ2.54VS-01-05P	5	10.16	12.70
XY-PZ2.54VS-01-06P	6	12.70	15.24
XY-PZ2.54VS-01-07P	7	15.24	17.78
XY-PZ2.54VS-01-08P	8	17.78	20.32
XY-PZ2.54VS-01-09P	9	20.32	22.86
.....			
XY-PZ2.54VS-01-40P	40	(PIN-1)X2.54	(PIN)X2.54

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.54PH H2.5 1xnPin SMT PC5.0 PA6.0 PB3.2 L11.0 6T (佳特)	
.X±0.3	X.*± 5°	CHK.	Jack	DWG NO. XY-PZ2.54VS-01-NP	
.XX±0.2	.X.*± 1°	DRA.	Can	PROJ.  CUSTOMER DRAWING	
.XXX±0.1	.XX.*± 0.5°	SIZE A4	SCALE 1:1	SHEET 1/1	REV. A