




Part No	Pin	A	B	C
FPC02-WF0.5-4PCR42	4	1.50	2.60	5.05
FPC02-WF0.5-5PCR42	5	2.00	3.10	5.55
FPC02-WF0.5-6PCR42	6	2.50	3.60	6.05
FPC02-WF0.5-7PCR42	7	3.00	4.10	6.55
FPC02-WF0.5-8PCR42	8	3.50	4.60	7.05
FPC02-WF0.5-9PCR42	9	4.00	5.10	7.55
FPC02-WF0.5-10PCR42	10	4.50	5.60	8.05
FPC02-WF0.5-11PCR42	11	5.00	6.10	8.55
FPC02-WF0.5-12PCR42	12	5.50	6.60	9.05
FPC02-WF0.5-13PCR42	13	6.00	7.10	9.55
FPC02-WF0.5-14PCR42	14	6.50	7.60	10.05
FPC02-WF0.5-15PCR42	15	7.00	8.10	10.55
.....		...		
FPC02-WF0.5-60PCR42	60	(60-1)*0.5	(60+1)*0.5+0.1	(60+6)*0.5+0.05

技术指标:

1. 额定电流: 0.5A
2. 温度范围: -40~85℃
3. 额定电压: 50V, AC/DC (等效)
4. 接触电阻: $\leq 0.03\Omega$
5. 绝缘电阻: $\geq 500M\Omega$

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE: 0.5C无锁立贴		
.X ± 0.15	X.* $\pm 1^{\circ}$	Alex	DWG NO.	FPC02-WF0.5-NPCR42	
.XX ± 0.10	.X.* $\pm$	Jack	PROJ.	CUSTOMER DRAWING	
.XXX ± 0.05	.XX.* $\pm$	Can	SIZE A4	SCALE 1:1	SHEET 1/1
				REV.	A