




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2024.08.23	阿树
A2	N/A	Ⓐ2 X1	产品尺寸变更	2025.10.21	阿树



- SPECIFICATIONS
- Voltage rating:600V AC/DC
 - Current rating:13A AC/DC
 - Withstanding Voltage:3500V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤15mΩ


PART NO.:

X9635 W V-02 H-N2 SN
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Row No.Pin No:XX-02~10Pin
⑤Category:H-Hollw Pin
⑥Material:N0-Nylon 66 UL94V-0;
N2-Nylon 66 UL94V-2
⑦Planting: SN-Bright tin plating

Poles	Dimensions(mm)	
	A	B
02	6.35	13.97
03	12.70	20.32
04	19.05	26.67
05	25.40	33.02
06	31.75	39.37
07	38.10	45.72
08	44.45	52.07
09	50.80	58.42
10	57.15	64.77

X9635WV-02H-N0SN	Nylon 66 UL94V-0	Phosphor Bronze	X9635HM
X9635WV-02H-N2SN	Nylon 66 UL94V-2		
PART NO	Material	Material(Pin)	Suitable XKB Housing



PCB LAYOUT

0.25 [0.010]
(Cut off Tad)

4.50 [0.177]

8.70 [0.343]

Ⓐ2

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 6.35mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X9635WV-02H-N2SN
APPROVED		SIZE: A4	DWG NO.: X-X9635WV-02H-N2SN

SCALE	PAGE	REVISION
N/A	1/1	A2