





技术指标:

1. 额定电流: 0.5A
2. 温度范围: $-40 \sim 85^{\circ}\text{C}$
3. 额定电压: 50V, AC/DC (等效)
4. 接触电阻: $\leq 0.03\Omega$
5. 绝缘电阻: $\geq 500\text{M}\Omega$

Part No	Pin	A	B	C
FPC02-YF0.5-4PCRH20	4	1.50	2.60	7.60
FPC02-YF0.5-5PCRH20	5	2.00	3.10	8.10
FPC02-YF0.5-6PCRH20	6	2.50	3.60	8.60
FPC02-YF0.5-7PCRH20	7	3.00	4.10	9.10
FPC02-YF0.5-8PCRH20	8	3.50	4.60	9.60
FPC02-YF0.5-9PCRH20	9	4.00	5.10	10.10
FPC02-YF0.5-10PCRH20	10	4.50	5.60	10.60
FPC02-YF0.5-11PCRH20	11	5.00	6.10	11.10
FPC02-YF0.5-12PCRH20	12	5.50	6.60	11.60
FPC02-YF0.5-13PCRH20	13	6.00	7.10	12.10
FPC02-YF0.5-14PCRH20	14	6.50	7.60	12.60
FPC02-YF0.5-15PCRH20	15	7.00	8.10	13.10
*****	***	**	****	*****
FPC02-YF0.5-60PCRH20	60	$(60-1)*0.5$	$(60+1)*0.5+0.1$	$(60+11)*0.5+0.1$

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.15	X.*±1°	APR. Alex	TITLE: 0.5-A全包拉拔式(正位)		
.XX±0.10	.X*±	CHK. Jack	DWG NO. FPC02-YF0.5-NPCRH20		
.XXX±0.05	.XX*±	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1/1