



REV.	REVISION DESCRIPTION	DATE	APPD











NOTES:
1. Rated voltage: 250V AC.DC
2. Rated current: 2A AC DC
3. lnsulation resistance: ⩾1000 MΩ
5. Withstand voltage: 800V AC/minute
6. Ambient temprature:-40℃～+105℃
7. Material : Nylon UL94V-0(2)
8. Matched RoHS criteria




Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
2X2	SAND-4Y	2.00	5.20	2X9	SAND-18Y	16.00	19.20
2X3	SAND-6Y	4.00	7.20	2X10	SAND-20Y	18.00	21.20
2X4	SAND-8Y	6.00	9.20	2X11	SAND-22Y	20.00	23.20
2X5	SAND-10Y	8.00	11.20	2X12	SAND-24Y	22.00	25.20
2X6	SAND-12Y	10.00	13.20	2X13	SAND-26Y	24.00	27.20
2X7	SAND-14Y	12.00	15.20	2X14	SAND-28Y	26.00	29.20
2X8	SAND-16Y	14.00	17.20	2X15	SAND-30Y	28.00	31.20


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD		
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL20041(SAND)-Y		TITLE: 2.00 mm Pitch Wire To Board Housing
.XX: ± 0.15	.X° : ± 2.0°	DR:Yuan Jun Rong	DATE:21/08/01	PART NO:
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD:Wu Hui	DATE:21/08/01	SCALE: N/A PAGE: 1/1
FINISH:		APPD:Ren An De	DATE:21/08/01	UNITS: mm REV.: A
DRAWING NO:				

REV.	REVISION DESCRIPTION	DATE	APPD







NOTES:
Rated voltage: 250V AC.DC
Rated current: 2A AC DC
Insulation resistance: ⩾1000 MΩ
Withstand voltage: 800V AC/minute
Ambient temprature:-40℃～+105℃
Wire range: AWG#30～#24
Materials:
Terminal: Phosphor bronze,Tin plated




SECTION A-A



SECTION B-B



SECTION C-C



PCB LAYOUT

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD		
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL20041(SAND)-T		TITLE: 2.0 mm pitch Crimping Terminal
.XX: ± 0.15	.X° : ± 2.0°			
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:2019/08/01	PART NO:
FINISH:		CHKD: Wu Hui	DATE:2019/08/01	SCALE: N/A / PAGE: 1/1
DRAWING NO:		APPD:Ren An De	DATE:2019/08/01	UNITS: mm / REV.: A