




序号	品名	材质
1	基座	LCP UL94V-0 本色
2	端子	磷青铜/表面镀锡

技术指标:

- 额定电流: 0.5A
- 温度范围: -40~85℃
- 额定电压: 50V, AC/DC (等效)
- 接触电阻: $\leq 0.03\Omega$
- 绝缘电阻: $\geq 500M\Omega$



Part No	Pin	A	B	C
FPC02-WF1.0-4PCR47	4	3.00	5.10	6.00
FPC02-WF1.0-5PCR47	5	4.00	6.10	7.00
FPC02-WF1.0-6PCR47	6	5.00	7.10	8.00
FPC02-WF1.0-7PCR47	7	6.00	8.10	9.00
FPC02-WF1.0-8PCR47	8	7.00	9.10	10.00
FPC02-WF1.0-9PCR47	9	8.00	10.10	11.00
FPC02-WF1.0-10PCR47	10	9.00	11.10	12.00
FPC02-WF1.0-11PCR47	11	10.00	12.10	13.00
FPC02-WF1.0-12PCR47	12	11.00	13.10	14.00
.....		...		
FPC02-WF1.0-36PCR47	36	(36-1)*1.0	(36+1)*1.0+0.10	38.00



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 1.0B黑色双面贴片式 (正位)	
.X±0.15	X.*±1°	CHK.	Jack	DWG NO. FPC02-WF1.0-NPCR47	
.XX±0.10	.X.*±	DRA.	Can	PROJ.  CUSTOMER DRAWING	
.XXX±0.05	.XX.*±	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A