







1. 极数 Number of poles: 2-16
2. 工作温度 Working Temperature: -40℃~+85℃
3. 额定电压 Voltage rating : 125V AC
4. 额定电流 Rated current : 1A
4. 接触电阻 Contact resistance: ≤30mΩ
5. 绝缘电阻 Insulation resistance: ≥100MΩ
6. 耐压 Withstand voltage : 250V AC
7. 端子 Terminal : 黄铜 Brass
8. 外壳 Housing : LCP



PCB. 焊接图
PCB. WELDING DRAWING

Part No	PIN	A	B	C	D
XY-SM2W-MXS-TB	2	1.25	0.00	4.40	7.50
XY-SM3W-MXS-TB	3	2.50	0.00	5.65	8.75
XY-SM4W-MXS-TB	4	3.75	2.50	6.90	10.00
XY-SM5W-MXS-TB	5	5.00	3.75	8.15	11.25
XY-SM6W-MXS-TB	6	6.25	5.00	9.40	12.50
XY-SM7W-MXS-TB	7	7.50	6.25	10.65	13.75
XY-SM8W-MXS-TB	8	8.75	7.50	11.90	15.00
XY-SM9W-MXS-TB	9	10.00	8.75	13.15	16.25
XY-SM10W-MXS-TB	10	11.25	10.00	14.40	17.50
XY-SM11W-MXS-TB	11	12.50	11.25	15.65	18.75
XY-SM12W-MXS-TB	12	13.75	12.50	16.90	20.00
XY-SM13W-MXS-TB	13	15.00	13.75	18.15	21.25
XY-SM14W-MXS-TB	14	16.25	15.00	19.40	22.50
XY-SM15W-MXS-TB	15	17.50	16.25	20.65	23.75
XY-SM16W-MXS-TB	16	18.75	17.50	21.90	25.00

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: WAFER 1.25 贴片	
≥0~2< ±0.20	±0.5°	CHK.	Jack	DWG NO. XY-SMNW-MXS-TB	
≥2~5< ±0.30		DRA.	Can	CUSTOMER DRAWING	
≥5 ±0.50		SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A