




		D		E	
REV.	DESCRIPTION	ECN NO.	NAME	DATE	



BOTTOM VIEW



RECOMMENDED PCB LAYOUT(TOP VIEW)

THICKNESS 0.8±0.05MM;DEFAULT TOLERANCE:±0.05

USB TYPE-C PIN ASSIGNMENTS

PIN	NUMBER	SIGNAL NAME	PIN	NUMBER	SIGNAL NAME
A1		GND	B12		GND
A2		SSTXp1	B11		SSRXp1
A3		SSTXn1	B10		SSRXn1
A4		Vbus	B9		Vbus
A5		CC1	B8		SBU2
A6		Dp1	B7		Dn2
A7		Dn1	B6		Dp2
A8		SBU1	B5		CC2
A9		Vbus	B4		Vbus
A10		SSRXn2	B3		SSTXn2
A11		SSRXp2	B2		SSTXp2
A12		GND	B1		GND

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN [®]	
DIM. TOL. .x ±0.30 .xx ±0.20 .xxx ±0.10 GENERAL ANGLE: x° ±10° x.x° ±8° x.xxx° ±5°		TITLE: USB C F SPLINT CONN. WITHOUT EMI PCB=1.0					
		DWG. NO.: UC22-6B24F00P11		CHECKED: MAX			
		PART NO.: UC22-6B24F00P11		DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 2 of 2	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL