








Part No	Pin	A	B	C
FPC02-YF1.0-4PCR55	4	3.00	5.15	11.00
FPC02-YF1.0-5PCR55	5	4.00	6.15	12.00
FPC02-YF1.0-6PCR55	6	5.00	7.15	13.00
FPC02-YF1.0-7PCR55	7	6.00	8.15	14.00
FPC02-YF1.0-8PCR55	8	7.00	9.15	15.00
FPC02-YF1.0-9PCR55	9	8.00	10.15	16.00
FPC02-YF1.0-10PCR55	10	9.00	11.15	17.00
FPC02-YF1.0-11PCR55	11	10.00	12.15	18.00
FPC02-YF1.0-12PCR55	12	11.00	13.15	19.00
.....		...		
FPC02-YF1.0-36PCR55	36	(36-1)*1.0	(36+1)*1.0+0.15	(36+7)*1.0



技术指标:

- 额定电流: 0.5A
- 温度范围: -40~85℃
- 额定电压: 50V, AC/DC (等效)
- 接触电阻: $\leq 0.03\Omega$
- 绝缘电阻: $\geq 500M\Omega$



序号	品名	材质
1	1.0A胶芯	LCP UL94V-0 本色
2	1.0A立贴端子	磷青铜/表面镀锡
3	1.0A锁条	LCP UL94V-0 黑色
4	1.0A焊片	黄铜/表面镀锡

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.15	X.*±1°	APR. Alex	TITLE: 1.0—A插拔端子 (H:2.5)		
.XX±0.10	.X*±	CHK. Jack	DWG NO. FPC02—YF1.0—NPCRH55		
.XXX±0.05	.XX*±	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1