




A		B		C		D		E	
				REV.	DESCRIPTION		ECN NO.	NAME	DATE



THICKNESS SEE TABLE1;DEFAULT TOLERANCE:±0.05

TABLE 1

P/N	DIM A	DIM B	DIM C	DIM D	THICKNESS OF THE PCB	QTY/TUBE	QTY/BOX
UC22-5B24F00P11	10.40	0.45	0.80	0.82	0.80±0.05MM	50	18000

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]	
DIM. TOL. .x ±0.30 .xx ±0.20 .xxx ±0.10		TITLE: USB C F SPLINT CONN. WITH EMI PCB=0.8&1.0						
GENERAL ANGLE: x.° ±10° x.x° ±8° x.xx° ±5°		DWG. NO.: UC22-5B24F00P11			CHECKED: MAX			
		PART NO.: UC22-5B24F00P11			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 2 of 2	DWG. SIZE: A4	LAYER: bxconn		