




NOTE:

1.MATERIAL SPECIFICATION:

- 1.HOUSING:HIGH TEMPERATURE RESISTANT PLASTIC,UL94 V-0.
- 2.TERMINAL: COPPER ALLOY(C18150)
- 3.MID PLATE: STAINLESS STEEL(SUS301)
- 4.FRONT SHELL: STAINLESS STEEL(SUS304)

2.PLATING SPECIFICATION:

- 2-1.TERMINAL:
Ni 50u" MIN. UNDER PLATED OVER ALL.
Au 1u" PLATED ON THE FUNCTIONAL AREA OF CONTACT.
Au G/F PLATED ON THE SOLDER AREA.

- 2-2.FRONT SHELL:
Ni 30u" MIN. UNDER PLATED OVER ALL.

- 2-3.MID PLATE PLATE:
CLEAR ONLY

3.MECHANICAL PERFORMANCE,

- 3-1.INSERTION FORCE: 0.5~2.0kgf.
- 3-2.REMOVAL FORCE: 0.8kgf~2.0kgf.
- 3-3.DURABILITY: 10000 CYCLES.

4.ELECTRICAL PERFORMANCE,

- 4-1. VOLTAGE RATING: 5V.
CURRENT RATING: 5A.
- 4-2. LLCR:
VBUS & GND PINS AND OTHER PINS: 40mA/PIN MAX.
LLCR MAX. CHANGE OF ALL PINS: 10mA.
- 4-3.INSULATION RESISTANCE: 100MΩ MIN
- 4-4.DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.


5. ENVIRONMENTAL PERFORMANCE:

- OPERATING TEMPERATURE: -40C~+85°C.

6.IR REFLOW:

- THE PEAK TEMPERATURE ON THE BOARD SHALL
BE MAINTAINED FOR 10 SECONDS AT 260°C.


DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.30	.X*± 10°	APR.	Alex	TITLE: USB CF 16PIN (L=8.35) WITH POST	
.XX±0.20	.X*± 8°	CHK.	Jack	DWG NO. TYPE-C-C04DT-1TDL835	
.XXX±0.10	.XX*± 5°	DRA.	Can	PROJ.  CUSTOMER DRAWING	
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A		



SECTION:A-A




USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND



RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 1.00MM;DEFAULT TOLERANCE:±0.05

DIMENSION IN mm		厦门市辛译精密电子有限公司			
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyeconn Electronics Co.,Ltd			
.X±0.30	X.*± 10°	APR.	Alex	TITLE: USB CF 16PIN (L=8.35) WITH POST	
.XX±0.20	.X*± 8°	CHK.	Jack	DWG NO. TYPE-C-C04DT-1TDL835	
.XXX±0.10	.XX*± 5°			CUSTOMER DRAWING	
		DRA.	Can	PROJ. 	
				SIZE A4	SCALE 1:1



	REEL	CARTON
CONNECTOR (PCS)	800	8000

DIMENSION IN mm		厦门市辛译精密电子有限公司			
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyeconn Electronics Co.,Ltd			
.X±0.30	X.*±10°	APR. Alex	TITLE: USB CF 16PIN (L=8.35) WITH POST		
.XX±0.20	.X.*±8°	CHK. Jack	DWG NO. TYPE-C-C04DT-1TDL835		
.XXX±0.10	.XX.*±5°	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1