





		D		E	
REV.	DESCRIPTION	ECN NO.	NAME	DATE	




主要技术参数、性能

The Main Thchnology Performance

额定电流、电压 Rate voltage.current	50mA DC12V
接触电阻 Contact resistance	≤100mΩ
按力 Operating force	±50gf
行程 Travel	0.20±0.10mm
绝缘电阻 Insulated resistance	≥100MΩ
介电强度 Dielectric strength	≥250VAC/1min



PCB.焊接图
PCB.WELDING DRAWING



CIRCUIT DIAGRAM

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN [®]	
DIM. TOL. 0.5~2 ±0.10 2~5 ±0.25 5~10 ±0.30 GENERAL ANGLE: ±0.5°		TITLE: TACT SWITCH					
		DWG. NO.: TS-1002S-TZXXXM		CHECKED: MAX			
		PART NO.: TS-1002S-TZXXXM		DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL