

技术参数：

- 1、所有材料符合ROHS2.0/REACH要求。
- 2、材质：PA66 白色
- 2、额定电流：3A，AC，DC；
- 3、额定电压：350V，AC，DC；
- 4、温度范围：-25℃~+85℃；
- 5、绝缘电阻： $\geq 1000M\Omega$ ；
- 6、耐压：500V，AC/minute.
- 7、产品料号：

Circuits	Dimensions (mm)		
	A	B	C
02	1.50	3.65	4.05
03	3.00	5.15	5.55
04	4.50	6.65	7.05
05	6.00	8.15	8.55
06	7.50	9.65	10.05
07	9.00	11.15	11.55
08	10.50	12.65	13.05
09	12.00	14.15	14.55
10	13.50	15.65	18.00
11	15.00	17.15	17.55
12	16.50	18.65	19.05
13	18.00	20.15	20.55
14	19.50	21.65	22.05
15	21.00	23.15	23.55
16	22.50	24.65	25.05

GENERAL TOLERANCES				DRAWN BY	罗荣程/2024.8.13	浙江深海电子有限公司	
0.X	±0.25	X.°	±3°	CHK. BY	朱江浩/2024.8.13		
0.XX	±0.12						
0.XXX	±0.05	X.X°	±0.5°	APRV. BY	姚 婷/2024.8.13		
UNIT	SIZE	SCALE		DRAWING NO.	1 OF 1	PROD. NAME	SH-MX1.5-NY
MM	A4	1:1		H15016-00	PART NO. A15003-nY-01 TITLE 1.50mm Pitch Crimp Housing Single Row		