






REV.	DESCRIPTION	DATE
A/0		2016.11.28
B/0	升B版	2024.8.7



- 技术参数:
- 1、所有材料符合ROHS2.0/REACH/HF要求。
 - 2、额定电流: 2A, AC, DC;
 - 3、额定电压: 250V, AC, DC;
 - 4、温度范围: -25℃~+85℃;
 - 5、接触电阻: $\leq 0.03\Omega$;
 - 6、绝缘电阻: $\geq 1000M\Omega$;
 - 7、耐压: 1000V, AC/minute.
 - 8、适用线规: AWG#28 to #24
 - 9、产品料号:

A20003 - n AB - 03 T1

孔位 ————— 电镀
产品类型 ————— T1:镀亮锡
AB:立贴针座 ————— 胶芯材质
03:LCP 米色

Circuits	Dimensions (mm)			
	A	B	C	D
2*2	2.00	6.00	4.90	3.00
2*3	4.00	8.00	6.90	3.00
2*4	6.00	10.00	8.90	3.00
2*5	8.00	12.00	10.90	5.00
2*6	10.00	14.00	12.90	7.00
2*7	12.00	16.00	14.90	9.00
2*8	14.00	18.00	16.90	11.00
2*9	16.00	20.00	18.90	13.00
2*10	18.00	22.00	20.90	15.00
2*11	20.00	24.00	22.90	17.00
2*12	22.00	26.00	24.90	19.00
2*13	24.00	28.00	26.90	21.00
2*14	26.00	30.00	28.90	23.00
2*15	28.00	32.00	30.90	25.00
2*16	30.00	34.00	32.90	27.00

3	吸盖 Cap	LCP (UL94V-0)	1	米色			
2	端子 Contact	黄铜	n*2	电镀(锡)：整个表面镀底镍20u~MIN, 再镀锡100u~MIN. .			
1	基座 Wafer	LCP (UL94V-0)	1	米色			
序号	名 称	材 料	数 量	附 注			
GENERAL TOLERANCES		DRAWN BY	朱江浩	浙江深海电子有限公司			
0.X	±0.25	X.°	±3°				
0.XX	±0.12	CHK. BY	丁尔特				
0.XXX	±0.05	APRV. BY	姚婷				
UNIT		SIZE	SCALE		DRAWING NO.	SHEET	PROD. NAME
MM	A4	1:1			H20015-00	1 OF 1	PART NO.
						TITLE	SH-PHB2.0-2XNALT
						2.0mm pitch 180° WAFER-SMT TYPE	
						A20003-nAB-03T1	