







由 Autodesk 教育版产品制作



性能:
额定电流: 3A
额定电压: 30V
耐电压: 500V
接触电阻: 30mΩ MAX
绝缘电阻: 500MΩ
工作温度: -55℃~+125℃
塑件(材质): PA9T
接触点(材质): 磷铜, 镀金5U

RECOMMENDED PCB LAYOUT
TOL:(±0.05)



Pin数	PART NO.	DIM A	DIM B
2P	BC-70-2PD400-5U-B	7.7	5.11
3P	BC-70-3PD400-5U-B	11.7	9.11
4P	BC-70-4PD400-5U-B	15.7	13.11
5P	BC-70-5PD400-5U-B	19.7	17.11
6P	BC-70-6PD400-5U-B	23.7	21.11

版本REV.	日期DATE	未注公差 TOLERANCE	JMECONN 东莞市文章济美电子有限公司	
2017050522	2017.05.05	X. ±0.35 X." ±4°		
		X. ±0.25 X.X' ±3°	品名ARTICLE: 电池连接器	
绘制DRAWN		X.XX ±0.15 X.XX ±2°		
		X.XXX ±0.05 X.XXX ±1°		
设计DES'D		视图方法 PROJECTION	图号MODEL: BC-70-NPD400-5U-B A4	
审核CHK'D				
批准APPV'D		比例SCALE:	单位UNIT: mm	页码SHEET: 共1页 第1页

由 Autodesk 教育版产品制作