


性能:

额定电流: 5.0A

额定电压: 30V

耐电压: 500V

接触电阻: 30mΩ MAX




绝缘电阻: 500MΩ

工作温度: -55℃~+125℃

使用寿命: 10000次以上


塑件(材质): LCP黑色

接触点(材质): 黄铜C2680, 接触面镀金3U"



RECOMMENDED PCB LAYOUT

TOP VIEW (.XX±0.05)



规格型号	DIM A	DIM B
BC-92-2PD190-B	7.0	5.0
BC-92-3PD190-B	10.5	8.5
BC-92-4PD190-B	14.0	12.0
BC-92-5PD190-B	17.5	15.5
BC-92-6PD190-B	21.0	19.0
BC-92-7PD190-B	24.5	22.5
BC-92-8PD190-B	28.0	26.0

版本REV.	更新标记REVISION	NOTE	日期DATE	未注公差 TOLERANCE	JMECONN 东莞市文章济美电子有限公司	
				X. ±0.35		
绘制DRAWN				X.X ±0.25	品名ARTICLE: 电池连接器	
				X.XX ±0.15		
设计DES'D				X.XXX ±0.05	图号MODEL: BC-92-NPD190-B	
				视图方法 PROJECTION		
审核CHK'D				比例SCALE:	单位UNIT: mm	
					页码SHEET: 共1页 第1页	A4