








由Autodesk教育版产品制作

F

E

B

A



RECOMMENDED PCB LAYOUT
TOL:(±0.05)

性能:

- 额定电流: 2.0A
- 额定电压: 12V
- 耐电压: 500V
- 接触电阻: 30mΩ
- 绝缘电阻: 500MΩ
- 工作温度: -40℃~+85℃
- 塑件(材质): LCP黑色
- 接触点(材质): 磷青铜, 触点镀金3U"

BC-76-8P460-C06-B	20.00	17.50	15.00
BC-76-7P460-C06-B	17.50	15.00	12.50
BC-76-6P460-C06-B	15.00	12.50	10.00
BC-76-5P460-C06-B	12.50	10.00	7.50
BC-76-4P460-C06-B	10.00	7.50	5.00
规格型号	A	B	C

版本REV. 更新标记REVISIONNOTE	日期DATE	未注公差 TOLERANCE	JMECONN 东莞市文章济美电子有限公司	
		X. ±0.35		
绘制DRAWN		X.X ±0.25	品名ARTICLE: 电池连接器	
设计DES'D		X.XX ±0.15		
审核CHK'D		X.XXX ±0.05	图号MODEL: BC-76-NP460-C06-B A4	
批准APPV'D		视图方法 PROJECTION		
		比例SCALE:	单位UNIT: mm	页码SHEET: 共1页 第1页