






性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 触点镀金3U",

使用寿命: 5000次以上

RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)

Pin数	PART NO.	DIM A
2Pin	BC-12-2P170-B	4.0
3Pin	BC-12-3P170-B	6.0
4Pin	BC-12-4P170-B	8.0
5Pin	BC-12-5P170-B	10.0
6Pin	BC-12-6P170-B	12.0
7Pin	BC-12-7P170-B	14.0
8Pin	BC-12-8P170-B	16.0

版本REV.	更版标记REVISION	NOTE	日期DATE	未注公差 TOLERANCE	JMECONN 东莞市文章济美电子有限公司 品名ARTICLE: 电池连接座 图号MODEL: BC-12-NP170-B A4	
				X. ±0.35		
				X.X ±0.25		
				X.XX ±0.15		
绘制DRAWN				X.XXX ±0.05	视图方法 PROJECTION	
设计DES' D						
审核CHK' D					比例SCALE: 3: 1	
批准APPV' D						
				单位UNIT: mm	页码SHEET: 共1页 第1页	