






REV.	DESCRIPTION	DATE
A/0		2023.3.27




技术参数:

- 1、所有材料符合ROHS2.0/REACH要求。
- 2、额定电流: 8A, AC, DC;
- 3、额定电压: 300V, AC, DC;
- 4、温度范围: -25℃~+85℃;
- 5、接触电阻: ≤0.015Ω;
- 6、绝缘电阻: ≥1000MΩ;
- 7、耐压: 1500V, AC/minute.
- 8、产品料号:

A42001 - n A - 10 T1
孔位
产品类型
A: 直插针座
电镀
T1: 镀亮锡
胶芯材质
10: PA66 本色



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)



pin位	A	B	pin位	A	B
2x1		5.6	2x7	25.2	30.8
2x2	4.2	9.8	2x8	29.4	35.0
2x3	8.4	14.0	2x9	33.6	39.2
2x4	12.6	18.2	2x10	37.8	43.4
2x5	16.8	22.4	2x11	42.0	47.6
2x6	21.0	26.6	2x12	46.2	51.8

2	端子 Contact	黄铜 Brass	n*2	电镀(锡)：整个表面镀底镍20u"MIN, 再镀锡100u". MIN.			
1	基座 Wafer	PA66 (UL94V-2)	1	透明本色			
序号	名 称	材 料	数 量	附 注			
GENERAL TOLERANCES		DRAWN BY	罗荣程/2024.8.17	浙江深海电子有限公司			
X.0	±0.30	X.°	±3°			CHK. BY	朱江浩/2024.8.17
O.X	±0.25					APRV. BY	姚 婷/2024.8.17
O.XX	±0.10	X.X°	±0.5°	SHEET	PROD. NAME SH-5569-4.2-NA		
UNIT	SIZE	SCALE		DRAWING NO.	1 OF 1		
MM	A4	1:1		H42001-00	PART NO.	A42001-nA-10T1	
				TITLE 4.2 mm pitch 180° WAFER-DIP TYPE			