





性能:

额定电流: 5.0A

额定电压: 30V

耐电压: 500V

接触电阻: 30mΩ Max




绝缘电阻: 500MΩ Min

工作温度: -40℃~+85℃


塑件(材质): LCP

接触点(材质): 磷铜, 触点镀金3U",

使用寿命: 10000次以上



RECOMMENDED PCB LAYOUT
TOL: (±0.05)



Pin数(N)	PART NO.	DIM A	DIM B	DIM C
3Pin	BC-45-3PD475-B	12.75	4.25	8.5
4Pin	BC-45-4PD475-B	17.0	8.5	12.75
5Pin	BC-45-5PD475-B	21.25	12.75	17.0
6Pin	BC-45-6PD475-B	25.5	17.0	21.25

版本REV.	更新标记REVISION	日期DATE	未注公差 TOLERANCE	JMECONN 东莞市文章济美电子有限公司	
			X. ±0.35	品名ARTICLE: 电池连接座	
			X.X ±0.25		
			X.XX ±0.15		
			X.XXX ±0.05		
绘制DRAWN			视图方法 PROJECTION	图号MODEL: BC-45-NPD475-B	
设计DES'D					
审核CHK'D				A4	
批准APPV'D					
比例SCALE:			单位UNIT: mm	页码SHEET: 共1页 第1页	