

NFC 60x45mm L110 CM1 Antenna

FEATURES



- Operating Frequency: 13.56 MHz
- RF Power: 2W
- RoHS: Yes
- Operating Temperature: -40 to +85°C



PRODUCTS

Part No.	Weight	Dimensions (L x WxH)	Cables Dimensions	Connector	Color
AINF011	2.1g	60*45.0*0.4mm	Φ 1.13*110mm	IPEX1	Black+Gray

SPECIFICATIONS


PARAMETER	SPECIFICATION
Frequency Bands, MHz	13.56MHz
Nominal Impedance	50 Ω
Max Power (ambient temp of 25°C)	2 Watts
Color	Black
Storage Temperature Range (°C)	-40° C to +85° C
Operational Temperature Range (°C)	-40° C to +85° C
Material Substance Compliance	REACH/RoHS Compliant
HSCODE	8517710000
UPC	

MyAntenna RF Technology Co., Ltd

ADD: No. RM 410, Country Garden Phoenix Wisdom Valley, No. 50 Tiezai Road, Baoan District, Shenzhen, P.R.China.

TEL: +86-0755-86503881 FAX: +86-0755-27801677 E-mail: nfc@imyantenna.com

ELECTRICAL DATA



HOUSING CONFIGURATIONS

