





性能:

额定电流: 5.0A

额定电压: 30V

耐电压: 500V

接触电阻: 30mΩ MAX




绝缘电阻: 500MΩ

工作温度: -55℃~+125℃

使用寿命: 10000次以上


塑件(材质): LCP黑色

接触点(材质): 黄铜C2680, 接触面镀金3U"



RECOMMENDED PCB LAYOUT

TOP VIEW (.XX±0.05)



规格型号	DIM A	DIM B
BC-62-2PD160-B	6.0	3.0
BC-62-3PD160-B	9.0	6.0
BC-62-4PD160-B	12.0	9.0
BC-62-5PD160-B	15.0	12.0
BC-62-6PD160-B	18.0	15.0
BC-62-7PD160-B	21.0	18.0
BC-62-8PD160-B	24.0	21.0

版本REV.	更新标记REVISION	NOTE	日期DATE	未注公差	TOOLURANCE	JMECONN 东莞市文章济美电子有限公司	
				X.	±0.35		
				X.X	±0.25		
				X.XX	±0.15		
绘制DRAWN				X.XXX	±0.05	品名ARTICLE: 电池连接器	
设计DES'D							
审核CHK'D				视图方法	PROJECTION	图号MODEL: BC-62-NPD160-B	
批准APP'D							
				比例SCALE:		单位UNIT: mm	页码SHEET: 共1页 第1页