









性能:

额定电流: 3.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -45℃~+85℃

使用寿命: 5000次以上

塑件(材质): PA9T黑色

接触点(材质): 黄铜C2680, 镀金3U

规格	DIM A	DIM B
BC-17-3PD127-B	4.8	1.8
BC-17-4PD127-B	6.4	3.4
BC-17-5PD127-B	8.0	5.0
BC-17-6PD127-B	9.6	6.6
BC-17-7PD127-B	11.2	8.2
BC-17-8PD127-B	12.8	9.8
BC-17-9PD127-B	14.4	11.4
BC-17-10PD127-B	16.0	13.0

RECOMMENDED PCB LAYOUT

TOP VIEW (.XX±0.05)

版本REV.	更新标记REVISION	日期DATE	未注公差 TOLERANCE	JMECONN 东莞市文章济美电子有限公司	
			X. ±0.35	品名ARTICLE: 电池连接器	
			X.X ±0.25		
			X.XX ±0.15		
绘制DRAWN			X.XXX ±0.05	图号MODEL: BC-17-NPD127-B	
设计DES'D			视图方法 PROJECTION		
审核CHK'D				A4	
批准APPV'D			比例SCALE:		
			单位UNIT: mm	页码SHEET: 共1页 第1页	