









RECOMMENDED PCB LAYOUT

TOP VIEW(. XX±0.05)

性能:

额定电流: 5.0A

额定电压: 30V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -55℃~+125℃

使用寿命: 10000次以上

塑件(材质): PA9T黑色

接触点(材质): 黄铜C2680, 镀金

规格	DIM A	DIM B
BC-13-2PD127-B	4.0	2.0
BC-13-3PD127-B	6.0	4.0
BC-13-4PD127-B	8.0	6.0
BC-13-5PD127-B	10.0	8.0
BC-13-6PD127-B	12.0	10.0
BC-13-7PD127-B	14.0	12.0
BC-13-8PD127-B	16.0	14.0

版本REV.	更版标记REVISION	NOTE	日期DATE	未注公差 TOLERANCE	JMECONN 东莞市文章济美电子有限公司	
				X. ±0.35		
绘制DRAWN				X.X ±0.25	品名ARTICLE:	
				X.XX ±0.15		
				X.XXX ±0.05	图号MODEL: BC-13-NPD127-B	
设计DES'D				视图方法 PROJECTION		
				审核CHK'D	A4	
批准APPV'D				比例SCALE:		
				单位UNIT: mm	页码SHEET: 共1页 第1页	