







性能:

额定电流: 5.0A

额定电压: 30V

耐电压: 500V

接触电阻: 30mΩ



绝缘电阻: 500MΩ

工作温度: -55℃~+125℃

使用寿命: 10000次以上

塑件(材质): LCP黑色

接触点(材质): 黄铜C2680, 镀金



RECOMMENDED PCB LAYOUT

TOP VIEW(.XX±0.05)

规格	DIM A	DIM B
BC-72-2PD190-B	8.0	6.0
BC-72-3PD190-B	12.0	10.0
BC-72-4PD190-B	16.0	14.0
BC-72-5PD190-B	20.0	18.0
BC-72-6PD190-B	24.0	22.0

版本REV.	更版标记REVISIONNOTE	日期DATE	未注公差 TOLERANCE	JMECONN 东莞市文章济美电子有限公司	
			X. ±0.35 X.° ±4°		
			X.X ±0.25 X.X' ±2'	品名ARTICLE:	
绘制DRAWN			X.XX ±0.15 X.XX ±0.5°		
设计DES'D			X.XXX ±0.05 X.XXX ±0.05°	图号MODEL:	
审核CHK'D			视图方法 PROJECTION		
批准APPV'D			比例SCALE:	单位UNIT: mm	

电池连接器

BC-72-NPD190-B

A4

页码SHEET: 共1页 第1页