





电池装配方向

BC-78-6PD630-C07-B	12.50	16.30	10.00	15.40
BC-78-5PD630-C07-B	10.00	13.80	7.50	12.90
BC-78-4PD630-C07-B	7.50	11.30	5.00	10.40
规格型号	A	B	C	D

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V


接触电阻: 30mΩ

绝缘电阻: 500MΩ


工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 镀金



RECOMMENDED PCB LAYOUT
TOL:(±0.05)

版本REV.	更新标记REVISIONNOTE	日期DATE	未注公差 TOLERANCE		JMECONN 东莞市文章济美电子有限公司	
			X. ±0.35	X.* ±4°		
			X.X ±0.25	X.X* ±3°		
绘制DRAWN			X.XX ±0.15	X.XX ±2°	品名ARTICLE: 电池连接座	
设计DES'D			X.XXX ±0.05	X.XXX ±1°		
		视图方法 PROJECTION				
审核CHK'D					图号MODEL:	BC-78-NPD630-C07-B
批准APPV'D			比例SCALE:		单位UNIT: mm	页码SHEET: 共1页 第1页
			A4			