






REV.	DESCRIPTION	DATE
A/0	新版发行	2023.5.8

- 技术参数:
- 1、所有材料符合ROHS2.0/REACH要求;
 - 2、材质: 磷铜, T=0.20;
 - 3、电镀(锡):
整个表面镀底镍20u"MIN, 再镀锡 100u"MIN;
 - 4、额定电流: 3A, AC, DC;
 - 5、额定电压: 250V, AC, DC;
 - 6、温度范围: -25℃~+85℃;
 - 7、接触电阻: ≤0.02Ω;
 - 8、适用线规: AWG28# to 22#;
 - 9、产品料号: A25001 - T - P T1

产品类型
T: 端子
主体材质
P: 磷青铜

电镀
T1: 镀亮锡



电镀后收料方向

GENERAL TOLERANCES				DRAWN BY 朱江浩/2023.05.08		浙江深海电子有限公司	
0.X	±0.25	X.°	±3°	CHK. BY	丁尔特/2023.05.08		
0.XX	±0.12			APRV. BY	姚婷/2023.05.08		
0.XXX	±0.05	X.X°	±0.5°			SHEET	PROD. NAME SH-XH-2.54-T
UNIT	SIZE	SCALE		DRAWING NO.		1 OF 1	PART NO. A25001-T-PT1
MM	A4	1:1		H25006-00		TITLE	